


L-Cover BLine Select WX01

BLine Select WX01 cover satinised L-shape 2000 mm for WT01

Article no.: 170373



Covering width



Bore/transmittance



Net height

TENDER TEXT

cover WT satinised L-shape 180x180° 73% PMMA W 32.5 x H 32.5 x L 2000 mm BILTON LEDON Technology L-Cover BLine Select WX01 Article 170373 The L-Cover BLine Select WX01 cover can be combined with all profiles from the WT family. The cover consists of Kunststoff and has a satiniert finish with a transmittance degree of 73 . Dimension (L x W x H): 2000 x 32.5 mm x Please note that cutting tolerances of +/- 2mm may occur.

L-Cover BLine Select WX01

BLine Select WX01 cover satinised L-shape 2000 mm for WT01

Article no.: 170373



MECHANICAL DATA

| | |
|--|------------------|
| Material | Kunststoff |
| Width [mm] | 32.5 |
| Length | 2000 |
| Covering width | 32.5 |
| Colour | White |
| Model | Lengthwise cover |
| Suitable for | L - Profil |
| Inflammability class of insulation material acc. with UL94 | HB |
| Surfacetreatment | satiniert |

TEMPERATURE TECHNICAL DATA

| | |
|-----------------------------|---------------|
| Ambient/storage temperature | + 10 ... + 50 |
| Thermal conductivity | 70 |
| Bore/transmittance | 73 |

PACKAGING INFORMATION

| | |
|-----------------------|----------|
| State of origin | DE |
| Customs tariff number | 94054231 |
| Net weight [g] | 94 |
| Gross weight [g] | 94 |
| Gross width [mm] | 32.5 |
| Gross height [mm] | 32.5 |
| Gross length [mm] | 2000 |
| Net width [mm] | 32.5 |
| Net height [mm] | 32.5 |
| Net length [mm] | 2000 |

SAFETY INFORMATION: Read the safety and installation instructions carefully and completely before commissioning. The operating instructions can be found at: www.better-light.at

DISCLAIMER OF WARRANTY: The technical information corresponds to the status at the time of printing and have been worked out to the best of our knowledge. However, errors and printing errors are reserved. Make sure that you always use the latest version of the data sheets. The latest data sheet can be found at: www.better-light.at